

# TPE™ Series Filter Cartridges

*Improved mechanical strength  
and corrosion resistance*

## Product Specifications

### Media:

Titanium, 316 Stainless Steel

### End caps:

Titanium, 316 Stainless Steel

### Gaskets/O-Rings:

Buna-N, EPR, Teflon Encapsulated  
Viton (O-Rings only), Teflon  
(Gasket only), Viton

### Micron ratings:

0.5, 1, 5, 10, 15, 35, 50, 100 µm

## Dimensions

### Nominal lengths:

5" 9.75" 10" 20" 30" 40"  
12.7 24.8 25.4 50.8 76.2 101.6 cm

### Outside diameter:

2.36" (60 mm)

## Operating Parameters

### Maximum operating temperature:

700°F (371°C)  
(threaded connection)

### Maximum differential pressure:

250 psid (17.4 bar) forward  
50 psid (3.5 bar) reverse

## TITANIUM POROUS METAL TECHNOLOGY

TPE series filters are porous metal filters designed for applications involving heat, gases, aggressive chemicals, cryogenics or polymers. Made from metal powder, that is sintered to form a rugged, fixed pore structure, TPE filters are made to withstand temperature extremes, high pressures and repeated cleaning/backwash cycles. There are no longitudinal seams, for improved mechanical strength and corrosion resistance. TPE filters are produced in a range of configurations and micron ratings to perform in a variety of liquid and gas applications.

## FEATURES & BENEFITS

- Constructed entirely of sintered titanium or 316 Stainless Steel powder — offers high corrosion resistance
- Cleanable/backwashable — allows for re-use, maximum economy
- High temperature sintering — no media migration, high pressure capabilities
- Various gasket/O-Ring materials and configurations — easily retrofits most systems

## TYPICAL APPLICATIONS


- Corrosive liquids and gases
- Cryogenic fluids
- High viscosity solutions
- Process steam
- High temperature liquids and gases
- Catalyst recovery

## TPE NOMENCLATURE INFORMATION

Filter Type	Material	Retention Rating (microns)		Nominal Length (in)	End Configuration	Gasket or O-Ring
TPE Series 60 mm Diameter	S 316 Stainless Steel	0.5	15	-5	P Double Open End (Hard Endcaps)	B Buna-N
		1	35	-9.75	P2 226/Flat Single Open End	E EPDM
		5	50	-10		N None
	T Titanium	10	100	-20	P3 222/Flat Single Open End	S Silicone
				-30	M1 ¾ Inch MNPT Threads	T Teflon encap. Viton (O-Rings only)
			-40	M2 1 Inch MNPT Threads	T Teflon Gasket	
<b>Example: TPET 5-40M1N</b>						
TPE	T	5		-40	M1	N

### TPE FLOW RATE

**Typical Flow Rate Clean Water at Ambient Temperature**  
(per 10" cartridge)



### REMOVAL EFFICIENCY

Beta Ratio Efficiency	Beta 200 99.5%	Beta 20 95%	Beta 10 90%
0.5 µm	0.5	0.3	0.1
1 µm	1.0	0.8	0.4
5 µm	5.0	3.0	1.0
10 µm	10.0	8.0	5.0
15 µm	15.0	12.0	10.0
35 µm	35.0	32.0	28.0

$$\text{Beta Ratio} = \frac{\text{Upstream particle counts}}{\text{Downstream particle counts}}$$

The micron ratings shown at various efficiency and beta ratio value levels were determined through laboratory testing, and can be used as a guide for selecting cartridges and estimating their performance. Under actual field conditions, results may vary somewhat from the values shown due to the variability of filtration parameters.

Testing was conducted using the single-pass test method, water at 2.5 gpm/10" cartridge. Contaminants included latex beads, coarse and fine test dust. Removal efficiencies were determined using dual laser source particle counters.

#### FOR MORE INFORMATION

Customer Service/Technical Support: 1-888-353-0303  
 Europe (UK): +44-1424-777791 | China: +86-21-5238-6576  
 Asia: +65-9635-7690

GTX-344 6-18



#### DISTRIBUTED BY

All information and recommendations appearing in this bulletin concerning the use of products described herein are based on tests believe to be reliable. However, It is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Graver Technologies as to the effects of such use or the results to be obtained. Graver Technologies assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations. TPE is a trademark of Graver Technologies, LLC.



Graver Technologies | 200 Lake Drive, Glasgow, DE 19702 | 302-731-1700 | 800-249-1990  
 Fax: 1-302-369-0938 | info@gravertech.com | www.gravertech.com

A member of The Marmon Group—A Berkshire Hathaway Company