



Graver Technologies

FILTRATION | SEPARATION | PURIFICATION



High Flow GF Series Filter Cartridges

Large Geometry Pleated Filters for High Flow

Graver High Flow Series filters feature a larger geometry to handle higher flows with fewer filter elements. The result is much faster, easier filter changeouts. In addition, the inside to outside flow allows for excellent dirt holding capacity, extending the time between filter changeouts. Filter housings are also available and because of the filter's high flow and dirt holding capacity, smaller systems are possible, reducing upfront capital costs.

Product Specifications

Media: Microfiberglass

Support/Cage: Polyester or polypropylene

End Caps: Polyacetal or polypropylene

Gaskets/O-Rings:

Buna-N, EPDM, Silicone, Viton

Micron rating: 1, 2.5, 4.5, 10, 20 μm

Dimensions

Nominal lengths:

20" 40" 60"

50.8 101.6 152.4 cm

Outside diameter: 6.0" (15.2 cm)

Surface Area:

24 ft² (2.2 m²) per 20" element

49 ft² (4.6 m²) per 40" element

73 ft² (6.8 m²) per 60" element

Operating Parameters

Maximum operating

temperature: 176°F (80°C)

Maximum differential pressure:

75 psid @ 70°F (5.2 bar @ 21°C)

30 psid @ 176°F (2.0 bar @ 80°C)

Maximum reverse pressure:

40 psid @ 70°F (2.8 bar @ 21°C)

Recommended change-out

pressure: 35 psid (2.4 bar)

Maximum flow rates*:

60" element up to 500 GPM (1892 lpm)

40" element up to 350 GPM (1325 lpm)

20" element up to 175 GPM (662 lpm)

*Consult factory for sizing assistance based on particle loads.

FEATURES & BENEFITS

- Materials of construction allow compatibility with some chemistries not served by all polypropylene elements
- 6" diameter, large geometry for high flows
- Absolute retention ratings from 1 to 20 microns
- Capable of flow rates up to 500 GPM in a single 60" element
- Inside-out flow retains contaminant even during changeout
- Outer cage prevents media extrusion problem experienced with some competitive offerings
- Unique Quad Seal gasket provides maximum seal integrity
- Retrofits competitive high flow filter housings
- Thermally bonded construction

TYPICAL APPLICATIONS

- Fuel Oil
- Chemicals
- Petrochemicals
- Solvents
- Oil & Gas

HIGH FLOW GF SERIES NOMENCLATURE INFORMATION

Product Series	Hardware Material	Retention Rating (microns)		Length (inches)	Gasket or O-Ring	Packaging	
HFGF Series	-P Polypropylene	-1	-10	-20	B Buna-N	Blank	Individual Box
	-A Acetal Caps Polyster Cage	-2.5	-20	-40	E EPDM	2 pk	2 Pack Box, 60" Only
		-4.5		-60	S Silicone	4 pk	4 Pack Box, 60" Only
					V Viton		
Example: HFGF-A-2.5-60E							
HFGF	-A	-2.5		-60	E		

HIGH FLOW GF PRESSURE DROP

Micron	Element Pressure Drop psid/gpm			Element Pressure Drop Mbar/M ³ /Hr		
	20"	40"	60"	20"	40"	60"
1	0.0394	0.0197	0.0131	11.9419	5.9709	3.9806
2.5	0.0183	0.0091	0.0061	5.5385	2.7692	1.8462
4.5	0.0144	0.0072	0.0048	4.3549	2.1775	1.4516
10	0.0095	0.0048	0.0032	2.8830	1.4415	0.9610
20	0.0069	0.0035	0.0023	2.0940	1.0470	0.6980

For chemical compatibility, flow rates, and temperature requirements please consult the factory or your local Graver distributor.

REMOVAL EFFICIENCY

Beta Ratio Efficiency	Beta 1000 99.9%	Beta 100 99%	Beta 10 90%
1 µm	1.0	0.6	0.2
2.5 µm	2.5	0.8	0.45
4.5 µm	4.5	4.2	1.0
10 µm	10.0	5.5	3.0
20 µm	20.0	15.0	10.0

$$\text{Beta Ratio} = \frac{\text{Upstream particle counts}}{\text{Downstream particle counts}}$$

The micron ratings shown at various efficiency and beta ratio value levels were determined through laboratory testing, and can be used as a guide for selecting cartridges and estimating their performance. Under actual field conditions, results may vary somewhat from the values shown due to the variability of filtration parameters.

Testing was conducted using the single-pass test method, water at 3 gpm/10" cartridge. Contaminants included latex beads, coarse and fine test dust. Removal efficiencies were determined using dual laser source particle counters.

FOR MORE INFORMATION

Customer Service/Technical Support: 1-888-353-0303
 Europe (UK): +44-1424-777791 | China: +86-21-5238-6576
 Asia: +65-9635-7690

GTX-331 10-16



All information and recommendations appearing in this bulletin concerning the use of products described herein are based on tests believe to be reliable. However, It is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Graver Technologies as to the effects of such use or the results to be obtained. Graver Technologies assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

DISTRIBUTED BY



Graver Technologies | 200 Lake Drive, Glasgow, DE 19702 | 302-731-1700 | 800-249-1990
 Fax: 1-302-369-0938 | info@gravertech.com | www.gravertech.com

A member of The Marmon Group—A Berkshire Hathaway Company